

2.4/5 GHZ 6 DBI 4 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH DART ATS-OP-245-6-1DART-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.485/5.15-5.85 GHz Gain: 6 dBi Polarization: Vertical Horizontal Beamwidth: 105°/110° Vertical Beamwidth: 65°/55° VSWR: ≤1.5:1, max 2.0 Isolation: >30 dB Impedance: 50 Ω Lightning Protection: None Max Input Power: 50 W per port



MECHANICAL SPECIFICATIONS

Dimensions: 11.12" L x 4.82" H x 1.08" D (282.5mm L x 122.5mm H x 27.5mm D) Weight: 1.5 lb (0.68 kg) Installation: Flush Mount to Wall Radome Material: ABS Connector: DART Number of Leads: 1 Cable Length: 36" (910mm)



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 158°F (-40 to 70°C) Wind Velocity: 134 mph (216 km/h) IP Rating: IP66


WARRANTY


2 Year Limited Warranty



2.4 GHZ

5.5 GHZ





The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2020 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM