

2.4/5 GHZ 7 DBI 4 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPTNC ATS-OP-245-7D-4RPTP-36

4

ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.485/5.15-5.85 GHz Gain: 7 dBi Polarization: 2 Vertical, 2 Horizontal Horizontal Beamwidth: $66^{\circ}/65^{\circ}$ Vertical Beamwidth: $66^{\circ}/62^{\circ}$ VSWR: \leq 1.5:1, max 2.0 Isolation: >30 dB Impedance: 50 Ω



MECHANICAL SPECIFICATIONS

Dimensions: 12" x 8.46" x 1.57" (305x215x40mm) Weight: 1.5 lb (0.68 kg) Installation: Flush Mount to Wall OR included Articulating Mount (included)



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 158°F (-40 to 70°C) Wind Velocity: 134 mph (216 km/h) IP Rating: IP66




Radome Material: ABS Connector: RPTNC Number of Leads: 4 Cable Length: 36" (910mm) Cable Type: ATS-195

WARRANTY

2 Year Limited Warranty



HORIZONTAL



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. ©2023 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM

VERTICAL