

2.4/5 GHZ 7 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPTNC ATS-OP-245-7D-6RPTP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.485/5.15-5.85 GHz

Gain: 7 dBi

Polarization: 3 Vertical, 3 Horizontal Horizontal Beamwidth: $66^{\circ}/65^{\circ}$ Vertical Beamwidth: $66^{\circ}/62^{\circ}$ VSWR: $\leq 1.5:1$, max 2.0 Isolation: > 30 dB Impedance: 50 Ω



MECHANICAL SPECIFICATIONS

Dimensions: 12.2" x 8.66"x 1.57" (310x220x40mm)

Weight: 1.5 lb (0.68 kg)

Installation: Flush Mount to Wall OR included Articulating Mount (included)



Radome Material: ABS Connector: RPTNC Number of Leads: 6

Cable Length: 36" (910mm) Cable Type: RG402 Plenum



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 158°F (-40 to 70°C)

Wind Velocity: 134 mph (216 km/h)

IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL

