

# 2.4/5/6 GHZ 8/10/10 DBI 10 ELEMENT PATCH ANTENNA ATS-OP-2456-81010-10MPC-36



#### **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 8/10/10 dBi

Polarization: 5 Vertical / 5 Horizontal Horizontal Beamwidth: 65°/45°/40° Vertical Beamwidth: 65°/45°/40°

VSWR: <2.0





# **MECHANICAL SPECIFICATIONS**

Dimensions: 15.4"x 15.4"x 2.24"(390x390x57mm)

Weight: 1.5 lb (0.68 kg)

Installation: Flush Mount to Wall or

Articulating wall/pole mount (included)

Radome Material: ABS Connector: 4MPC & 6MPC Number of Leads: 10 Cable Length: 36" (910mm) Cable Type: RG316



## **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Due to LPI requirements, indoor only

IP Rating: IP66


# **WARRANTY**

2 Year Limited Warranty



### **HORIZONTAL**

### **VERTICAL**





# 2.4/5/6 GHZ 8/10/10 DBI 10 ELEMENT PATCH ANTENNA ATS-OP-2456-81010-10MPC-36

