

PATCH ANTENNA WITH SMA ATS-OP-LTE-3-2SP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 698-960/1710-2690/3300-3800MHz

Gain: 3/3/3 dBi

Polarization: Horizontal

Horizontal Beamwidth: 75°/70°/75° Vertical Beamwidth: 75°/70°/75°

VSWR: <2.0





MECHANICAL SPECIFICATIONS

Dimensions: 10"x 9"x3.5" (254x228.6x88.9mm)

Weight: 2.2 lbs. (1 kg)

Installation: Flush Mount to Wall OR included Articulating Mount

Radome Material: ABS Connector: SMA Number of Leads: 2

Cable Length: 36" (910mm) Cable Type: ATS-200



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 158°F (-40 to 70°C)

Wind Velocity: 134 mph (216 km/h)

IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL

