




Formed Wire Deadend for Alumoweld® Strand 20M

by FARGO
Catalog ID: AWDE4126

Formed Wire Deadend for 20M Alumoweld® Guy Strand

- For Alumoweld® Guy Strand
- Alumoweld® wire construction
- 20,000lb (89.0kN) maximum RBS



* Representative image

Product Details

General

Application	Deadend for Alumoweld® Guy Strand
Color Code	Yellow
Material	Aluminum Clad Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359395591

Dimensions

Length	36 in
Nominal Guy Wire Size	20M Alumoweld®
Weight	2.200 lb

Conductor Related

Conductor Diameter - Maximum	0.474 in
Conductor Diameter - Minimum	0.431 in
Conductor Diameter Range	0.431 - 0.474
Conductor Type	Alumoweld®
Guy Wire Type	Alumoweld®

Logistics

Pallet Quantity	490 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com