



B060403CH

by Wiegmann
Catalog ID: B060403CH

N12 JIC Continuous Hinge 6X4X3 Carbon Steel - Gray

- Bodies fabricated from 14 gauge and doors fabricated from 16 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Lids are sealed with closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided for mounting optional panels securely. External screw clamps are quick and easy to operate. Standard continuous hinge. Grounding provisions provided.

Product Details

General

Application	Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door provides convenient access. Designed to provide protection from dust, dirt, oil, and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Hinged Cover
Finish Type	Textured
Latches Type	Clamps
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725331253

Dimensions

Depth	3 in
Height	6 in
Weight	3 lb
Width	4 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes