



B060604SC

by Wiegmann
Catalog ID: B060604SC

N12 JIC Screw-Cover 6X6X4 Carbon Steel - Gray

B-SC SERIES - 14 GAUGE CARBON STEEL NEMA 12 JIC SCREW COVER ENCLOSURE -ENCLOSURE
SIZE 6.00 IN X 6.00 IN X 4.00 IN.

- Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts of holes. Lids are sealed with closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided to secure optional back panel. Captivated cover screws are provided which thread into sealed wells to prevent leakage through cover. Grounding provisions provided.

Product Details

General

Application	Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection from dirt, dust, oil, and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Textured
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725330553

Dimensions

Depth	4 in
Height	6 in
Weight	4.9 lb
Width	6 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes