



## B161406CHQR

by Wiegmann  
Catalog ID: B161406CHQR

N12 JIC Continuous Hinge Quick Release 16X14X6 Carbon Steel - Gray

- Bodies fabricated from 14 gauge and doors fabricated from 16 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Lids are sealed with closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided for mounting optional panels securely. External quick release latches secure cover. Standard continuous hinged secures cover. Grounding provisions provided.

### Product Details

#### General

Application	Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door with quick-release latching provide convenient access. Designed to provide protection from dust, dirt, oil, and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Hinged Cover
Finish Type	Textured
Latches Type	Quick-Release Latches
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725331956

#### Dimensions

Depth	6 in
Height	16 in
Weight	20 lb
Width	14 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 12
UL Listed	Yes