


BA123024DD

by CMC

Catalog ID: BA123024DD



Outdoor Meter, Instrument Transfer & Substation Equipment Enclosures, NEMA 3R, Board Size 27" x 21"

- Mounting Board is 3/4" exterior grade treated plywood in standard. Add "-AP" for aluminum back-plate at extra charge
- Standard double swinging doors with stainless steel lift-off hinges, 3-point locking handle. Doors have brackets, which hold them in the open position
- Material is .090 aluminum, .125 on request (add "-H")
- HUBS provided when requested at extra charge
- 4" louvers with screens (standard)
- Ground lug is Al-Cu lug furnished (standard).

Special sizes and modifications available upon request.

Product Details

General

Material	Aluminum
UPC	192663133253

Dimensions

Cubic Capacity	8640 cu.in
Depth	12 in
Height	24 in
Width	30 in

CONNECTOR MANUFACTURING COMPANY

3501 Symmes Road

Hamilton, Ohio 45015 - 1369

513 - 860 - 4455(Press 2 for Customer Service and Sales)

To email customer Service: jrex@cmclugs.com