


# BA133240DD

by CMC

Catalog ID: BA133240DD



Outdoor Meter, Instrument Transfer & Substation Equipment Enclosures, NEMA 3R, Board Size 29" x 37"

- Mounting Board is 3/4" exterior grade treated plywood in standard. Add "-AP" for aluminum back-plate at extra charge
- Standard double swinging doors with stainless steel lift-off hinges, 3-point locking handle. Doors have brackets, which hold them in the open position
- HUBS provided when requested at extra charge
- 4" louvers with screens (standard)
- Ground lug is Al-Cu lug furnished (standard).

Special sizes and modifications available upon request.

## Product Details

### General

Material	Aluminum
UPC	192663133260

### Dimensions

Cubic Capacity	16640 cu.in
Depth	13 in
Height	40 in
Width	32 in