

BACT123636DD-4LUG


by CMC

Catalog ID: BACT123636DD-4LUG

Current Transformer Enclosures For Bar Type Current Transformers NEMA 3R

- 6 500MCM-4 hole connectors mounted on fiberglass reinforced thermoset polyester. The fiberglass is mounted on H-BAR EXTRUSION and is adjustable
- Standard swinging door with stainless steel lift off hinges and stainless steel 3-point locking handle. Doors have brackets, which hold them in the open position
- Material is .090 aluminum, unpainted (standard). Optional powder coat at extra charge(contact your rep). .125 material uponrequest add "-H"
- I-DLA-250 Ground lug (standard)
- HUBS provided when requested at extra charge

Special sizes & modifications available upon request



Product Details

General

Material	Aluminum
UPC	192663132645

Dimensions

Cubic Capacity	15552 cu.in
Depth	12 in
Height	36 in
Width	36 in