


BACT124848-4LUG

by CMC

Catalog ID: BACT124848-4LUG

Enclosures for bar type current transformers Nema 3R

- MOUNTING DEVICE: 6 500MCM-4 hole connectors mounted on fiberglass reinforced thermoset polyester. The fiberglass is mounted on H-BAR EXTRUSION and is adjustable
- DOOR: Standard swinging door with stainless steel lift off hinges and stainless steel 3-point locking handle. Doors have brackets, which hold them in the open position
- MATERIAL: .090 aluminum, unpainted (standard). Optional powder coat at extra charge (contact your rep). .125 material upon request add "-H"



Product Details

Dimensions

Cubic Capacity	27648 cu.in
Depth	12 in
Height	48 in
Width	48 in