



* Representative image

Deadend

by ANDERSON
Catalog ID: BDE70N

Deadend, Straight line, Bronze, 4/0 SOL - 350MCM CU, Conductor Range 0.46- 0.70 in, Fitting: None.

- For use with copper or CopperWeld conductor
- Add "S" for socket or "C" for clevis fitting options

Product Details

General

Fitting Type	None
Material	Bronze
Material - Body	Bronze Alloy
Material - Bolt	Galvanized Steel
Material - Hardware	Galvanized Steel
Product Category	Straight Line
Strength Rating - Ultimate Body	8000 lb
Style	BDE
Type	Bolted
U-Bolts	2 in
UPC	096359291633

Dimensions

Diameter - Bolt	0.5 in
Weight	6.370 lb

Conductor Related

Conductor Diameter - Maximum	0.7 in
Conductor Diameter - Minimum	0.46 in
Conductor Diameter Range	0.46 - 0.7

Logistics

Carton Quantity	10 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com