



BMAC-129TB

by CMC

Catalog ID: BMAC-129TB

Thru-bolt mount, For mounting one 3kVA thru 50kVA transformer, reclosure or sectionalizer, having 12" ANSI/NEMA type A lugs (no adaptor plate required),
Transformer size : 3kVA thru 50 kVA

- Ground wire clamp and 5/8" or 3/4" hot-dipped galvanized transformer mounting hardware furnished with the mount.
- Attaches to the pole with two 5/8" diameter thru-bolts (not supplied) at 7-1/16" hole spacing.
- 3" wide slot(s) standard - can be used with stainless steel band kits (sold separately).
- Mounts equipment 6" or 9" from the pole.
- Extension kit available by adding "-5 to BMAC XXXX"

Product Details

General

Type	Bolted Pole Mount Bracket
UPC	192663126064