



BMAC-156SS

by CMC

Catalog ID: BMAC-156SS

Banded transformer cluster mounts, mounts 3 KVA thru 167 KVA Transformers

- Cluster made with high strength extruded 6061-T6 aluminum alloy
- With ground wire clamp
- Ultimate load 15,000# total - 5,000# per position
- 12" or 24" NEMA transformer spacing
- EE1-NEMA type B
- Extension kit available by adding "-5 to BMAC XXXX"
- Mounts one transformer 6" from pole

Product Details

General

Type	Bolted Pole Mount Bracket
------	---------------------------

CONNECTOR MANUFACTURING COMPANY

3501 Symmes Road

Hamilton, Ohio 45015 - 1369

513 - 860 - 4455(Press 2 for Customer Service and Sales)

To email customer Service: jrex@cmclugs.com