



BMAC-3156SS-36-H

by CMC

Catalog ID: BMAC-3156SS-36-H

Banded transformer cluster mounts, Mounts 3KVA Thru 167 KVA Transformers, Stainless Steel band, for jumbo transformer spacing, Mounts three transformers 6" from pole for pole sizes 17' - 19.5".

- Cluster made with high strength extruded 6061-T6 aluminum alloy.
- With ground wire clamp.
- Ultimate load 15,000# total - 5,000# per position.
- EE1-NEMA type B lugs.
- Three mounting bands for additional strength 12", 24", or 36" NEMA transformer spacing
- Designed specifically for use on "Jumbo Transformers" to allow the transformers to be mounted further apart. Up to 120 degrees on 9" pole diameters.
- B-Bolt pack included (standard). -For A-pack add "A" to end of catalog number & For C-pack add "C", for AB-pack add "AB".
- Completely assembled.
- Stainless steel banding cut to special lengths as specified by customer.
- Ideal for under build construction on lug transmission poles.
- Adaptor plates available for 167KVA thru 250 KVA.
- Extension kit available by adding "-5 to BMAC XXXX"

Product Details

General

Material	Aluminum
Type	Banded Pole Mount Bracket
UPC	192663141081



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

