



BN4060604

by Wiegmann
Catalog ID: BN4060604

N4 JIC Lift-Off Cover 6X6X4 Carbon Steel - Gray

- Bodies fabricated from 14 gauge and doors fabricated from 16 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided to secure optional panel. Stainless steel screws and clamps on four sides of cover to assure water tight seal. Grounding provisions provided. Optional back panels and terminal kits must be ordered separately.

Product Details

General

Application	Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection where equipment is hosed down, very wet, or in outdoor applications.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Lift Off
Finish Type	Textured
Latches Type	Clamps
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725377251

Dimensions

Cubic Capacity	216 cu.in
Depth	6 in
Height	6 in
Weight	5 lb
Width	6 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4
UL Listed	Yes