



## BN4060604SSA

by Wiegmann  
Catalog ID: BN4060604SSA

N4X JIC Lift-Off Cover 6X6X4 316 Stainless Steel

- Bodies and doors fabricated from 16 gauge type 316 stainless steel. Continuously welded seams ground smooth, less knockouts or holes. Sealed with poured-in-place polyurethane gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided to secure optional panel. Stainless steel screws and clamps on four sides of cover assure watertight seal. Grounding provisions provided. Optional panels and terminal kits must be ordered separately.

## Product Details

### General

Application	Provides unmatched protection for housing electrical components in highly corrosive environments. This enclosure is used in indoor and outdoor settings that are frequently wet or have constant exposure to water, other liquids, or contaminants.
Construction	Continuously Welded Seams
Cover Type	Lift Off
Knockouts	No
Latches Type	Clamps
Listings	UL, CSA
Material	316 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	BN4-SSA
Type	Enclosure
UPC	786725871452

### Dimensions

Actual Depth	7.500 in
Actual Height	4.250 in
Actual Width	7.130 in
Cubic Capacity	224 cu.in

Depth	8 in
Height	4 in
Weight	5 lb
Width	7 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• CSA</li><li>• IEC</li><li>• UL</li></ul>
Nema Rating	4X
UL Listed	Yes