



BN4161406

by Wiegmann
Catalog ID: BN4161406

N4 JIC Lift-Off Cover 16X14X6 Carbon Steel - Gray

- Bodies fabricated from 14 gauge and doors fabricated from 16 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided to secure optional panel. Stainless steel screws and clamps on four sides of cover to assure water tight seal. Grounding provisions provided. Optional back panels and terminal kits must be ordered separately.

Product Details

General

Application	Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection where equipment is hosed down, very wet, or in outdoor applications.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Lift Off
Finish Type	Textured
Latches Type	Clamps
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725377503

Dimensions

Cubic Capacity	3584 cu.in
Depth	16 in
Height	16 in
Weight	22 lb
Width	14 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4
UL Listed	Yes