



BN4161406AL

by Wiegmann
Catalog ID: BN4161406AL

N4X JIC Lift-Off Cover 16X14X6 Aluminum

- Bodies and doors fabricated from .080-inch thick (2 millimeters) 5052-H32 aluminum. Continuously welded seams ground smooth, less holes or knockouts. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided to secure optional panel. Stainless steel screws and clamps on four sides of cover to assure water tight seal. Optional panels and terminal kits must be ordered separately. Grounding provisions provided.

Product Details

General

Application	Designed as an instrument housing or junction box for electrical, electronic, or pneumatic components. It is ideal for applications where a lightweight, corrosion resistant enclosure is required.
Construction	Continuously Welded Seams
Cover Type	Lift Off
Knockouts	No
Latches Type	Clamps
Listings	UL, CSA
Material	Aluminum
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	BN4-AL
Type	Enclosure
UPC	786725376872

Dimensions

Actual Depth	16.5 in
Actual Height	6.500 in
Actual Width	14.500 in
Cubic Capacity	1785 cu.in
Depth	17 in

Height	7 in
Weight	9 lb
Width	15 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4X
UL Listed	Yes