

Cable Spacer, Bronze

by ANDERSON
Catalog ID: BPCS0808

Bronze Cable Spacer, 8 in Spacing, range 0.811 - 1.031. SPACER, BRZ .811-1.031 IN, 8 IN L



* Representative image

Product Details

General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359292142

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	6.076 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.811 in
Conductor Diameter Range	0.811 - 1.031
Conductor Spacing	8 in
Conductor Type	Copper

Logistics

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com