



Cable Spacer, Bronze

by ANDERSON
Catalog ID: BPCS100212

Bronze Cable Spacer, 25 in Spacing, range 0.998 - 1.152. SPACER, BRZ .998-1.152 IN, 2.5 IN L



* Representative image

Product Details

General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359292159

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	2.940 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Diameter - Maximum	1.152 in
Conductor Diameter - Minimum	0.998 in
Conductor Diameter Range	0.998 - 1.152
Conductor Spacing	2.5 in
Conductor Type	Copper

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com