



* Representative image

Righthand Opening, 14.4kV, 110kV LIW, 600A Fused By-Pass Switch with 100 Amp Type C Fuse Tube.

by CHANCE Utility
Catalog ID: BPF11C

Righthand Opening, 14.4kV, 110kV LIW, 600A Fused By-Pass Switch with 100 Amp Type C Fuse Tube.

Product Details

General

| | |
|---------------------------------------|---------------------------------------|
| Blade Type | Solid Copper (two blade truss-member) |
| Color - Insulator | Sky Gray |
| Contact | Silver |
| Description - Replacement Fuse Holder | T710-112T |
| Insulator Type | N/A |
| Material - Base | Galvanized Steel per ASTM A153 |
| UPC | 096359387787 |

Electrical Ratings

| | |
|--|------------------------------------|
| BIL | 110 kV |
| Creep and Leakage Distance | 15.5" (393.7mm) |
| Current Overload - 8hr Emergency | 1080 A (switch circuit) |
| Interrupt Rating | 10,000 A |
| Reference Voltage Limit - Minimum | 14.4kV |
| Temperature Rise - Max. | 15.9° C (Fuse Circuit) |
| Temperature Rise - Max. at 600A | 25.7° C (switch circuit) |
| Voltage - Maximum | 15 kV |
| Withstand Current - Short Time (1 sec) | 25kA, symmetrical (switch circuit) |
| Withstand Current - Short Time (10 cycles) | 65kA peak (switch circuit) |

Certifications and Compliance

| | |
|----------------------|------------------------------------|
| Industry Standard(s) | All Applicable ANSI/IEEE Standards |
|----------------------|------------------------------------|

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com

