

# Straight Blade Devices 125V, 2 Pole, 3 Wire Grounding USB Charger Receptacles



## Features

- Four USB ports 5 Amp, 5V DC, type A, class 2.0
- Switch activated port door; when open enables power; when closed, all power is switched off, for a “zero” no-load draw
- Tamper-Resistant decorator duplex receptacle
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

## Ordering Information

Description	Device Color	UPC#	Catalog Number
USB Charger 4 Port Outlet, four USB type 2.0 ports, 5 Amp, 5 Volt DC, decorator	Black	781786193604	USBB4BK

## Listings

cETLus listed to UL131

## Specifications

Face	RTP
Base	RTP
LED	Green Indicator
Mounting Strap	Galvanized steel
Auto Self-grounding staple	Stainless steel
Mounting Screws	Zinc plated steel
Terminal Screws	Plated steel
USB Port	Stainless Steel

## Performance

### Electrical

Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Port	Stainless steel Rated for 10,000 plug insertions and removal

### Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



## Resources

[eCatalog](#)

Dimensions in Inches (mm)

Bryant Electric • An affiliate of Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 323-2792 • Specifications subject to change without notice