



Locking Devices, Industrial, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White

By Bryant
Catalog # 70530NC

Locking Devices, Industrial, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

Specifications

Standards - RoHS Compliance Status	CM
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L5-30R

Conductor

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	2-Pole
Conductor Range	#12 AWG to #8 AWG

Current

Amperage Rating	30 A
Voltage Rating Description	125 V
Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A



Voltage Rating	125 V
Connectivity	Screw Terminals

Dimensions

Length	2.13 in
Display Size	Standard Sized Product
Height	3.90 in
Width	2.13 in
Dimensions	2.13 in x 2.13 in x 3.90 in

General

Color	Black, White
Style	Internal Cord Clamp
UPC	781786688797
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite

Logistics

Pallet Quantity	1680
Carton Quantity	10

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)