



Locking Devices, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White

By Bryant
Catalog # 70530NP

Locking Devices, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L5-30P

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	2-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current



Amperage Rating	30 A
Voltage Rating Description	125 V
Current/Amperage Rating Description	30 Amp
Current Rating	30 A
Voltage Rating	125 V
Connectivity	Screw Terminals
Phase	Single Phase

Dimensions

Length	2.13 in
Display Size	Standard Sized
Height	2.86 in
Width	2.13 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

Color	Black, White
Style	Internal Cord Clamp
UPC	781786688803
Type	Plugs
Material - Mounting Hardware	Cord Mounted
Item Type	30A Triple Gripper Nylon Plug
Material	Composite

Logistics

Pallet Quantity	2250
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand