



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 50A 250V, 2-Pole 3- Wire Grounding, 6-50R

By Bryant
Catalog # 9650NC

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 50A 250V, 2-Pole 3- Wire Grounding, 6-50R, Gray, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 50A 250V
- 2-Pole 3- Wire Grounding

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Nema Rating	6-50R

Conductor

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Number Of Poles	2-Pole
Conductor Range	#6 AWG

Current

Amperage Rating	50 A
Voltage Rating Description	250 V
Current Rating	50 A
Voltage Rating	250 V
Connectivity	Pressure Terminal Screws



Current / Amperage Rating	50 A
Dimensions	
Display Size	Standard Sized Product
Weight	1.2 lb.

General

Color	Gray
Style	Extra Heavy Duty
Series	Industrial Series
UPC	781786732254
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	Standard
Material	Composite

Logistics

Pallet Quantity	1020
Carton Quantity	10

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)