

1PBS750HD

by Burndy
Catalog ID: 1PBS750HD

Prop 65 Notice

UV Rated Black UNITAP



Product Details

General

Hex Key	3/8
Installation Torque Recommended in-lb	500 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	4
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480810

Dimensions

Dimension - Height inch	3.01
Dimension - L Length Overall mm	267
Dimension - Length Overall inch	10.53

Electrical Ratings

Amperage Rating	535 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - Copper Str Size Range	6 AWG-750 KCMIL
-----------------------------------	-----------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)