



1PL2503

by Burndy
Catalog ID: 1PL2503

Prop 65 Notice

UV Black Covered Distribution Connectors, #10-250, 2.97 in L, 2.07 in W.

Features: UV Rated Plastisol Covered AL6061-T6 Aluminum Body Saves Time By Eliminating The Need For Taping, Oxide Inhibitor Pre-Installed Inhibits Moisture And Contaminants From Entering The Contact Area, Range-Taking Capability Reduces The Number Of Connectors Carried In Inventory, UL486B Listed, AL9CU, 600 V 90 DEG C, UNITAP Rated For Code Conductor Only, Wire Entry: Single, Torque: 275 IN-LB, Hex Size (key): 5/16 IN, Conductor Size (run - Range): 10 AWG - 250 KCML, Type Of Insulation: UV Rated Plastisol, Number Of Ports: 3, Wire Strip Length: 1 IN

Product Details

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Hex Key	5/16
Installation Torque Recommended in-lb	275 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	3
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194° F
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810286890
UPC 12 Digit	7818102868900

Dimensions

Dimension - Height fraction	2-1/8 in
Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.97 in
Dimension - Screw Size inch	5/8
Dimension - Width fraction	2-7/100 in
Dimension - Width inch	2.07 in
Dimension - Width mm	53 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	10 AWG-250 kcmil
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	10 AWG-250 kcmil
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)