


1PLMD25010

by Burndy
Catalog ID: 1PLMD25010

Mounted Black Tap Connector, 10 Ports, Double Side Entry, #10-250 kcmil, 11.16 IN L, 2.64 IN W



Product Details

General

Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	10
Physical Attribute - Number of Screws	12
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
Trade Name	UNITAP™
UPC	781810307564
UPC 12 Digit	7818103075644

Dimensions

Dimension - Height fraction	2-1/4 in
Dimension - Height inch	2.13
Dimension - L Length Overall mm	283
Dimension - Length Overall inch	11.16
Dimension - Width inch	2.64
Dimension - Width mm	67 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	10 AWG-250 kcmil
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	10 AWG-250 kcmil

Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)