

# 25X150HEBBOX

by Burndy  
Catalog ID: 25X150HEBBOX

Prop 65 Notice

Silicon Bronze Bolt, 1-12" L, Hexagonal bolts



## Product Details

### General

Application	<ul style="list-style-type: none"> <li>• Grounding</li> <li>• Distribution</li> <li>• Substation</li> <li>• Transmission</li> </ul>
Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	80 LBS/in
Material	Bronze, Silicon (DURIUM is a trademark)
Trade Name	DURIUM™
UPC	781810819012
UPC 12 Digit	7818108190122

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.250 in
Dimension - Length Overall inch	1.5 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)