

## 25X250HEBET

by Burndy  
Catalog ID: 25X250HEBET

Electro Tin Plate 1/4 x 2.50 Bolt

Coupler Assembly



### Product Details

#### General

Braid	Braided Copper
Debris Shield Type	Aluminum Foil
Item Type	HDMI Cables
Material - Insulation	30% Glass Filled LCP
Material - Jacket	CM
Type	HDMI

#### Dimensions

Outside Diameter	0.375 in
------------------	----------

#### Electrical Ratings

Amperage Rating	0.5 A
Current / Amperage Rating	0.5 A
Current Rating	0.5 A
Resistance	30 mili ohms Max
Voltage Rating	40 kV

#### Conductor Related

Conductor Size	#36 AWG
Conductor Type	Copper
Number Of Conductors	15
Strands	1

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)