

## 25X300HEBET

by Burndy  
Catalog ID: 25X300HEBET

Prop 65 Notice

Electro Tin Plated Silicon Bronze Hexagonal Head Bolt, 3.00 IN L, 1/4 IN-20 Thread Size



### Product Details

#### General

Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	80 LBS/in
UPC	781810249222
UPC 12 Digit	7818102492222

#### Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Minimum Pack Quantity	500
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)