

25X75HEBET

by Burndy
Catalog ID: 25X75HEBET

Prop 65 Notice

Electro Tin Plated Silicon Bronze Bolt, 1/4-20 IN Thread, Stud Length: 3/4 IN, Hexagonal Head



Product Details

General

Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	80 LBS/in
UPC	781810114339
UPC 12 Digit	7818101143399

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)