

## 38X175HEBET

by Burndy  
Catalog ID: 38X175HEBET

Prop 65 Notice

3/8 x 1.75 Electro Tin Plated Bolt



## Product Details

### General

|                                       |               |
|---------------------------------------|---------------|
| Connector Type                        | Bolt - Hex    |
| Installation Torque Recommended in-lb | 240 LBS/in    |
| Trade Name                            | DURIUM™       |
| UPC                                   | 781810463451  |
| UPC 12 Digit                          | 7818104634511 |

### Dimensions

|                                |          |
|--------------------------------|----------|
| Dimension - B Length fraction  | 1-3/4 in |
| Dimension - B Length inch      | 1.75 in  |
| Dimension - Bolt Size fraction | 3/8      |
| Dimension - Bolt Size inch     | 0.375 in |
| Dimension - Thread Size        | 3/8-16   |
| Dimension - Threads per inch   | 16       |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 250 |
|-----------------------|-----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)