

## 38X175OSBBOX

by Burndy  
Catalog ID: 38X175OSBBOX

Prop 65 Notice

3/8 x 1.75 Oval Shank Bolt



## Product Details

### General

Connector Type	Bolt - Oval Shank
Installation Torque Recommended in-lb	240 LBS/in
Material	Bronze, Silicon (DURIUM is a trademark)
UPC	781810362037
UPC 12 Digit	7818103620377

### Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)