

38X200HSSBUSA

by Burndy
Catalog ID: 38X200HSSBUSA

Prop 65 Notice

3/8 x 2.00 Stainless Steel Bolt



Product Details

General

Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	240 LBS/in
Material	Stainless Steel
UPC	781810330401
UPC 12 Digit	7818103304011

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)