

# 50X125HEBBOX

by Burndy  
Catalog ID: 50X125HEBBOX

Prop 65 Notice

Silicon Bronze Bolt, 1.25 in L, Hexagonal bolts, Thread size: 1/2-13.

Features: Thread Size: 1/2-13, Package: Box, Stud Length: 1-1/4 IN



## Product Details

### General

|                                       |   |
|---------------------------------------|---|
| Application                           | <ul style="list-style-type: none"> <li>• Grounding</li> <li>• Distribution</li> <li>• Substation</li> <li>• Transmission</li> </ul> |
| Connector Type                        | Bolt - Hex  |
| Installation Torque Recommended in-lb | 480 LBS/in  |
| Material                              | Bronze, Silicon (DURIUM is a trademark)   |
| Sub Brand                             | HARDWARE BOLT, DURIUM   |
| Trade Name                            | DURIUM™   |
| Type                                  | HEB, Hexagonal Bolts  |
| UPC                                   | 781810011768  |
| UPC 12 Digit                          | 7818100117688   |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - B Length fraction   | 1-1/4 in |
| Dimension - B Length inch       | 1.25 in  |
| Dimension - Bolt Size fraction  | 1/2      |
| Dimension - Bolt Size inch      | 0.5 in   |
| Dimension - Length Overall inch | 1.25 in  |
| Dimension - Thread Size         | 1/2-13   |
| Dimension - Threads per inch    | 13       |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)