

50X200HSSBBOX

by Burndy
Catalog ID: 50X200HSSBBOX

Prop 65 Notice

Stainless Steel Bolt, Stud Length: 2 IN, Hexagonal Head.

Features: Manufactured from 18-8 nonmagnetic material, Stud Length: 2 IN



Product Details

General

Application	For Use On Outdoor Connector Applications
Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	480 LBS/in
Material	Stainless Steel
Sub Brand	HARDWARE BOLT
Type	HSSB, Hexagonal Bolts
UPC	781810361146
UPC 12 Digit	7818103611466

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)