

## 50X250HSSBBOX

by Burndy  
Catalog ID: 50X250HSSBBOX

Prop 65 Notice

Stainless Steel Hexagonal Head Bolt, 2.50 IN L, 1/2 IN-13 Thread Size.

Features: Manufactured from 18-8 nonmagnetic material, Stud Length: 2-1/2 IN



### Product Details

#### General

Application	For Use On Outdoor Connector Applications
Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	480 LBS/in
Material	Stainless Steel
Sub Brand	HARDWARE BOLT
Type	HSSB,Hexagonal Bolts
UPC	781810361535
UPC 12 Digit	7818103615355

#### Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.5 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)