

50X3000SBBOX

by Burndy
Catalog ID: 50X3000SBBOX

1/2 x 3.00 Oval Shank Bolt



Product Details

General

Connector Type	Bolt - Oval Shank
Installation Torque Recommended in-lb	480 LBS/in
Material	Stainless Steel
UPC	781810462010
UPC 12 Digit	7818104620100

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)