

# 50X550HEBBOX

by Burndy  
Catalog ID: 50X550HEBBOX

Prop 65 Notice

1/2 x 5.50 Silicon Bronze Hex Bolt



## Product Details

### General

Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	480 LBS/in
Material	Bronze, Silicon (DURIUM is a trademark) Ductile Iron
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	SC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
Trade Name	DURIUM™
UPC	781810339091
UPC 12 Digit	7818103390911

### Dimensions

Clevis Opening	0.875 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimension - B Length fraction	5-1/2 in
Dimension - B Length inch	5.5 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	2.625 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in

### Conductor Related

Conductor Diameter - Maximum	0 in
------------------------------	------

Conductor Spacing	0 in
-------------------	------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)