

ASA250U

by Burndy
Catalog ID: ASA250U

Prop 65 Notice

Copper Stacking Adapter, 2 Slots, 250 kcmil, Al/Cu Rated, Tin Plated.

Features: The HYSTACK Adaptor Is Specially Designed To Allow Standard Terminals To Be Stacked On Two Or Four Hole NEMA Transformer Or Equipment Terminal Pads, HYSTACK Is Tin-Plated, High-Conductivity Aluminum To Provide Optimum Corrosion Resistance, Only Three Sizes Accommodate Terminals From 250 MCM Through 1000 MCM To Help Keep Costly Inventories To A Minimum, Height: 0.77 IN, Width: 1 IN



Product Details

General

Application	For Aluminum And Copper Terminals
Installation Torque Recommended in-lb	480 LBS/in
Material	Aluminum
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	HYSTACK
Temperature Rating	194° F
Trade Name	HYSTACK™
Type	Stacking Adapters
UPC	781810521007
UPC 12 Digit	7818105210077

Dimensions

Dimension - Bolt Size inch	2.75 in
Dimension - Height fraction	7/9 in
Dimension - Height inch	0.77 in
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.78 in
Dimension - Outside Diameter inch	0.87 in
Dimension - Pad Width inch	1.00 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
-------------------------	---

Conductor - AL Str Size Range	1/0 AWG-250 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	1/0 -250 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)