



## ASA800U

by Burndy  
Catalog ID: ASA800U

Prop 65 Notice

Copper Stacking Adapter, 2 Slots, 800 kcmil, Al/Cu Rated, Tin Plated.

Features: The HYSTACK Adaptor Is Specially Designed To Allow Standard Terminals To Be Stacked On Two Or Four Hole NEMA Transformer Or Equipment Terminal Pads, HYSTACK Is Tin-Plated, High-Conductivity Aluminum To Provide Optimum Corrosion Resistance, Only Three Sizes Accommodate Terminals From 250 MCM Through 1000 MCM To Help Keep Costly Inventories To A Minimum, Width: 1 IN, Height: 1.13 IN

## Product Details

### General

Application	For Aluminum And Copper Terminals
Installation Torque Recommended in-lb	480 LBS/in
Material	Aluminum
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	HYSTACK
Temperature Rating	194° F
Trade Name	HYSTACK™
Type	Stacking Adapters
UPC	781810521021
UPC 12 Digit	7818105210211

### Dimensions

Dimension - Bolt Size inch	3.50 in
Dimension - Height fraction	1-1/8 in
Dimension - Height inch	1.13 in
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.78 in
Dimension - Pad Width inch	1.00 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
-------------------------	---

Conductor - AL Str Size Range	1/0 AWG-800 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	1/0 -800 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)