



AYP900

by Burndy
Catalog ID: AYP900

Aluminum Compression Pin Adapter, 900 kcmil, 0.91" Plug Dia, 1.82" Plug Length, Al/Cu Rated, Tin Plated.

Product Details

General

Color Code	Gray
Connector Type	Pin Terminal
Die Index	303
Insulation	Y
Insulation Type	SANTOPRENE
Material	Aluminum
Physical Attribute - Number of Crimps Required	4
Pin Type	Straight
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYPLUG™
Type	Aluminum Pin Adapters
UPC	621945437401
UPC 12 Digit	6219454374011

Dimensions

Dimension - A Outside Diameter inch	1.50 in
Dimension - B Length inch	2.17 in
Dimension - B Outside Diameter inch	0.91 in
Dimension - L Length Overall mm	108 mm
Dimension - P inch	1.82 in
Dimension - Strip Length inch	2-3/8

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000 V

Conductor Related

Conductor - AL Str Size	900 kcmil
-------------------------	-----------

Conductor - Copper DLO Size	-
Conductor - Copper Flex I Size	-
Conductor - Copper Str Size	600 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)