



B10960

by Burndy
Catalog ID: B10960

Mold Connector, BCC-6, Conductor Size: 4/0 AWG - 750 KCMIL, Tools: B38-0309-00 Flint Ignitor, Accessories: B38-3922-00 Mold Cleaning Brush.

Features: BCC-6 Type Molds Are Used To Join Horizontal Parallel Tap To Run Connections, The Tap Cable Is Over The Run Cable, Size Range Is 6 AWG Through 4/0 AWG Concentric Stranded Copper Conductors, Required Tools: B38-0309-00 Flint Ignitor, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, Conductor Type: Concentric Stranded Copper

Product Details

General

Application	For Joining Horizontal Parallel Tap To Run Connections
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Type	Molds
UPC	781810491607
UPC 12 Digit	7818104916077

Conductor Related

Conductor - Copper Str Run	750 Kcmil
Conductor - Copper Str Tap	4/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)