



## B1271

by Burndy  
Catalog ID: B1271

Mold, Horizontal Parallel Tap, 6 AWG (Run & Tap), 25 Weld Metal.

Features: BCC-6 Type Molds Are Used To Join Horizontal Parallel Tap To Run Connections, The Tap Cable Is Over The Run Cable, Size Range Is 6 AWG Through 4/0 AWG Concentric Stranded Copper Conductors, Includes: Handle, Conductor Type: Concentric Stranded Copper, Cartridge Type: Standard, Required Tools: B38-0309-00 Flint Ignitor, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp

## Product Details

### General

Application	For Joining Horizontal Parallel Tap To Run Connections
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Type	Molds
UPC	781810377260
UPC 12 Digit	7818103772600

### Conductor Related

Conductor - Copper Str Run	6 AWG
Conductor - Copper Str Tap	6 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU C Str-Tap</li> </ul>

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)