



## B1596

by Burndy  
Catalog ID: B1596

Mold, Horizontal through Cable to Ground Rod, 4/0 AWG, 150 Weld Metal, 3/4" Ground Rod.

Type BCR-3 Molds Are Used To Join Horizontal Through Run Cable To The Side Of A Vertical Ground Rod, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Ground Rod Size: 3/4 IN, Conductor Type: Concentric Stranded Copper, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, B38-0304-00 File, Required Tools: B38-0309-00 Flint Ignitor, Cartridge Type: Standard

## Product Details

### General

Application	For Joining Horizontal Through Run Cable To The Side Of A Vertical Ground Rod
Mounting Type	Ground
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810387597
UPC 12 Digit	7818103875977

### Conductor Related

Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Tap</li> <li>• Rod-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)