



## B2160

by Burndy  
Catalog ID: B2160

Mold, Horizontal Through Cable to Ground Rod, 4 AWG, 90 Weld Metal, 3/4" Ground Rod.

Features: Type BCR-3 Molds Are Used To Join Horizontal Through Run Cable To The Side Of A Vertical Ground Rod, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Ground Rod Size: 3/4 IN, Conductor Type: Concentric Stranded Copper, Required Tools: B38-0309-00 Flint Ignitor, Cartridge Type: Standard, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, B38-0304-00 File

## Product Details

### General

|              |   |
|--------------|---|
| Application  | For Joining Horizontal Through Run Cable To The Side Of A Vertical Ground Rod |
| Sub Brand    | BURNDYWELD  |
| Trade Name   | BURNDYWeld®   |
| Type         | Molds   |
| UPC          | 781810388273  |
| UPC 12 Digit | 7818103882733   |

### Conductor Related

|                                  |  |
|----------------------------------|--|
| Conductor - Copper Str Tap       | 4 AWG  |
| Conductor - Copper Str Tap Range | 4 AWG  |
| Conductor - Rod Size             | 3/4 in   |
| Conductor - Rod Size Range       | 3/4 in   |
| Conductor Type                   | <ul style="list-style-type: none"> <li>• CU C Str-Tap</li> <li>• Rod-Size</li> </ul> |

### Certifications and Compliance

|                              |    |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)